



PC prerequisites



Contents



Search for revisions From year (and earlier): From month (and earlier): Tag filter:

Diff selection: Mark the radio boxes of the revisions to compare and hit enter or the button at the bottom.

Legend: **(cur)** = difference with latest revision, **(prev)** = difference with preceding revision, **m** = minor edit.

(newest | oldest) View (newer 50 | older 50) (20 | 50 | 100 | 250 | 500)

- [\(cur | prev\)16:13, 9 October 2019](#) . . (21,187 bytes) (-145) [Reviewed: [16:14, 9 October 2019](#) | | [Expert: [Aproved](#), [Technical writer: \[Approved\]\(#\)](#), [Maintainer: \[Approved\]\(#\)](#)]]
- [\(cur | prev\)09:35, 14 March 2019](#) [m](#) . . (20,032 bytes) (+10) . . (Reverted edits by [Sebastien Gandon](#) ([talk](#)) to last revision by) ([Tag: Rollback](#))[[automatically approved](#)] [Reviewed: [09:35, 14 March 2019](#) | | [Expert: [Aproved](#), [Technical writer: \[Approved\]\(#\)](#), [Maintainer: \[Approved\]\(#\)](#)]]
- [\(cur | prev\)14:15, 20 February 2019](#) [m](#) . . (20,032 bytes) (0) [Reviewed: [14:17, 20 February 2019](#) | | [Expert: [Aproved](#), [Technical writer: \[Approved\]\(#\)](#), [Maintainer: \[Approved\]\(#\)](#)]]
- [\(cur | prev\)14:10, 8 February 2019](#) [m](#) . . (20,809 bytes) (+21) [Reviewed: [11:21, 11 February 2019](#) | | [Expert: [Aproved](#), [Technical writer: \[Approved\]\(#\)](#), [Maintainer: \[Approved\]\(#\)](#)]]
- [\(cur | prev\)13:55, 15 January 2019](#) . . (20,788 bytes) **(+20,788)** . . (â Linux PC)[[automatically approved](#)] [Reviewed: [13:55, 15 January 2019](#) |]

(newest | oldest) View (newer 50 | older 50) (20 | 50 | 100 | 250 | 500)