

Contents

1. Reading tips	2
2. Main Page	3

Reading tips

The content format pdf is not supported by the content model wikitext.

Return to [Main Page](#).

View source for Main Page

You do not have permission to edit this page, for the following reasons:

- The action you have requested is limited to users in one of the groups: **Administrators**, **Editors**, **Reviewers**, **Selected_editors**, **ST_editors**.
- The action "Read pages" for the draft version of this page is only available for the groups **ST_editors**, **ST_readers**, **Selected_editors**, **sysop**, **reviewer**

You can view and copy the source of this page.

This article provides a few tips for easy reading of this user guide. **Browsing** "Chrome and Firefox browsers are recommended." The user guide contains hundreds of articles (aka pages). As for any wiki website, an article might refer to tens of other articles, which might themselves refer to tens of other articles (and so on). It may be tempting to follow these links at the risk of moving away from the original article. The articles are designed to be, as far as possible, self-sufficient. With this in mind, it is good practice to keep the main article open in your browser, and to open any article linked by the main article in a new browser tab. Focus on the main article is hence maintained. **Article restricted to STMicroelectronics employees** As STMicroelectronics employee, you access the user guide through an intranet URL (internal user guide). This user guide might contain information that is restricted to STMicroelectronics employees, and is therefore not included in the extraction of the user guide delivered to our customers (the delivered user guide). Consequently, if you want to send customers any information extracted from the internal user guide, you must take care that "it doesn't contain any restricted information". There are 2 ways to identify restricted information: * An article that belongs to the `<nowiki>[[Category:ST internal]]</nowiki>` category is fully restricted * In an article, the information under the following banner is restricted `{{InternalInfo| Restricted information}}` **Links** Any link, either to an article of the user guide or to an internet website, appears in `blue`. Example: * `[[Main Page|Link to the user guide Main Page]]`. * `[https://www.st.com Link to the STMicroelectronics website]`. Note the arrow icon that shows that the link leads to another site. **Image, clickable image and clickable image maps** An image might be: * a normal image - the image doesn't link to any destination * a clickable image - the entire area of the image links to a single destination * a clickable image map - some areas of the image link to multiple destinations Move your mouse pointer over the images below to see what the mouse pointer and the display looks like for each image. `{| |+ Image types available in the user guide ! Normal image !! Clickable image !! Clickable image map |-` | The image below simply shows the logo for the STM32 MP1 Series | If you click on the image, you are redirected to the user guide main page | If you click on the butterfly, you are redirected to the user guide main page. If you click on "STM32 MP1", you are redirected to the STMicroelectronics website (`[https://www.st.com st.com]`) `|-` | `[[File: STM32MP1 logo.png|center|link=]]` | `[[File: STM32MP1 logo.png|center|link=Main Page|text|Link to the user guide Main Page]]` | `{{ ImageMap|Image:STM32MP1 logo.png {{!}} frame {{!}} center{{!}}` Example of clickable image map `rect 55 17 172 118 [[Main Page|Link to the Main Page]] rect 34 123 169 153 [https://www.st.com Link to the STMicroelectronics website] }}` **Commands** Any command that is executed on the board (through the remote Terminal or the Wayland Terminal) starts with `{{Board$}}`, while any command executed on the host PC (through the local Terminal) starts with `{{PC$}}`. Example: `{{Board$}} pwd` means that the "pwd" command shall be executed on the board: it will print the name of the current directory on the board. `{{PC$}} pwd` means that the "pwd" command is executed on the host PC: it prints the name of the current directory on the host PC. `<noinclude> [[Category:MainMenuTab2]] {{PublicationRequestId | 8430 | 2018-09-04 | PhilipS}} </noinclude>`

Templates used on this page:

- [Template:Info \(view source\)](#)
- [Template:STDarkBlue \(view source\)](#)
- [Template:STYellow \(view source\)](#)

[Return to Main Page.](#)

IMPORTANT NOTICE – READ CAREFULLY

STMicroelectronics NV and its subsidiaries ("ST") reserve the right to make changes, corrections, enhancements, modifications, and improvements to ST products and/or to this document at any time without notice. Purchasers should obtain the latest relevant information on ST products before placing orders. ST products are sold pursuant to ST's terms and conditions of sale in place at the time of order acknowledgment.

Purchasers are solely responsible for the choice, selection, and use of ST products and ST assumes no liability for application assistance or the design of purchasers' products.

No license, express or implied, to any intellectual property right is granted by ST herein.

Resale of ST products with provisions different from the information set forth herein shall void any warranty granted by ST for such product.

ST and the ST logo are trademarks of ST. For additional information about ST trademarks, refer to www.st.com/trademarks. All other product or service names are the property of their respective owners.

Information in this document supersedes and replaces information previously supplied in any prior versions of this document.

© 2023 STMicroelectronics – All rights reserved