



DAC Linux driver



DAC Linux driver

Stable: 16.01.2020 - 15:01 / Revision: 16.01.2020 - 14:56

Contents

1 Article purpose	2
2 Short Description	2
3 Configuration	2
3.1 Kernel configuration	2
3.2 Device tree	3
4 How to use	3
5 How to trace and debug	3
6 Source code location	4
7 References	4

1 Article purpose

This article introduces the Linux[®] driver for the DAC^[1] internal peripheral:

- Which DAC features are supported by the driver
- How to configure, use and debug the driver
- What is the driver structure, and where the source code can be found.

2 Short Description

The DAC Linux[®] driver (kernel space) is based on the IIO framework.

It implements the IIO **direct mode**, to perform single conversions independently on each channel.

3 Configuration

3.1 Kernel configuration

Activate the DAC^[1] Linux[®] driver in the kernel configuration using the Linux Menuconfig tool: Menuconfig or how to configure kernel (enable CONFIG_STM32_DAC).

```
Device Drivers --->
  <*> Industrial I/O support --->
    Digital to analog converters --->
      <*> STMicroelectronics STM32 DAC
```

3.2 Device tree

Refer to the [DAC device tree configuration](#) article when configuring the DAC Linux kernel driver.

4 How to use

In "IIO direct mode", conversions can be done directly via sysfs. See [How to do a simple DAC conversion using the sysfs interface](#).

5 How to trace and debug

Refer to [How to trace with dynamic debug](#) for how to enable debug logs in the driver and in the Framework.

Refer to [How to debug with debugfs](#) for how to access the DAC registers.

The DAC has system wide dependencies towards other key resources:

- **runtime power management** can be disabled, for example it may be forced **on** via *power/control* sysfs entry:

```
Board $> cd /sys/devices/platform/soc/40017000.dac/40017000.dac\:dac@1/
Board $> cat power/autosuspend_delay_ms
2000
Board $> cat power/control
auto # kernel is allowed to automatically suspend
the ADC device after autosuspend_delay_ms
Board $> echo on > power/control # force the kernel to resume the DAC device
(e.g. keep clocks and regulators enabled)
```



It might be useful to disable runtime power management, in order to dump registers by any means or to check clock and regulator usage (see example below).

- **clock**^[2] usage can be verified by reading *clk_summary*:

```
Board $> cat /sys/kernel/debug/clk/clk_summary | grep dac
dac12_k          0      0      0      32000      0 0
                dac12      1      2      0      98303955 0 0
```

- **regulator**^[3] tree and usage usage can be verified (e.g. use count, open count and regulator reference voltage) as follows:



```
Board $> cat /sys/kernel/debug/regulator/regulator_summary
regulator          use open bypass voltage current      min      max
-----
v3v3                4   5     0  3300mV    0mA  3300mV  3300mV
vdda                1   2     0  2900mV    0mA  2900mV  2900mV
  40017000.dac      0mV      0mV
  48003000.adc      0mV      0mV
```

- `pinctrl`^[4] usage can be verified by reading `pinmux-pins`:

```
Board $> cd /sys/kernel/debug/pinctrl/soc\:\:pin-controller@50002000/
Board $> cat pinmux-pins | grep dac
pin 4 (PA4): device 40017000.dac function analog group PA4
pin 5 (PA5): device 40017000.dac function analog group PA5 # check pins are assigned
to DAC and configured as "analog"
```

6 Source code location

The DAC source code is composed of:

- `stm32-dac-core` driver to handle common resources such as `clock` or `regulator` used as reference voltage and common registers.
- `stm32-dac` driver to handle the resources available for each DAC such as channel configuration or output buffer handling (power-down mode).

7 References

- 1.01.1 DAC internal peripheral
- Clock overview
- Regulator overview
- Pinctrl overview

Digital-to-analog converter (Electronic circuit that converts a binary number into a continuously varying value.)

Industrial I/O Linux subsystem

System File System (See <https://en.wikipedia.org/wiki/Sysfs> for more details)

Analog-to-digital converter. The process of converting a sampled analog signal to a digital code that represents the amplitude of the original signal sample.