



File:STM32MP15 example command local terminal.png

---

File:STM32MP15 example command local terminal.png



[unchecked revision]	[quality revision]
<p><b>Revision as of 14:13, 29 January 2019 (view source)</b>                      imported&gt;Frq08471                      (uploaded a new version of "File:STM32MP15 example command local terminal.png")                      Older edit</p>	<p><b>Latest revision as of 08:46, 12 February 2019 (view source)</b>                      Maintenance script (talk   contribs)                      (Maintenance script uploaded a new version of File:STM32MP15 example command local terminal.png)</p>

(No difference)



---



**Latest revision as of 08:46, 12 February 2019**

---



## File history

Click on a date/time to view the file as it appeared at that time.

	Date/Time	Thumbnail	Dimensions	User	Comment
current	08:46, 12 February 2019		800 × 480 (53 KB)	Maintenance script (talk   contribs)	
	14:06, 13 November 2017		1,280 × 720 (65 KB)	Fred988 (talk   contribs)	

- You cannot overwrite this file.



---

## File usage

---

The following 3 pages link to this file:

- [STM32MP15 Discovery kits - Starter Package](#)
- [STM32MP15 Evaluation boards - Starter Package](#)
- [Subpart - STM32MP15 - Starter Package](#)



---

## Metadata

---

This file contains additional information, probably added from the digital camera or scanner used to create or digitize it. If the file has been modified from its original state, some details may not fully reflect the modified file.

Horizontal resolution	47.24 dpc
Vertical resolution	47.24 dpc