



File:STM32MP15 example command local terminal.png

File:STM32MP15 example command local terminal.png



- File
- File history
- File usage
- Metadata

Tue Oct 17, 03:49 PM

```
Wayland Terminal
sh-4.3# ifconfig
eth0      Link encap:Ethernet  HWaddr 00:0c:29:14:00:00
          inet addr:10.10.10.10      Bcast:10.10.10.255  Mask:255.255.252.0
          inet6 addr: fe80::1000:1000:1000:1000/64 Scope:Link
          UP BROADCAST RUNNING MULTICAST  MTU:1500  Metric:1
          RX packets:333 errors:0 dropped:0 overruns:0 frame:0
          TX packets:43 errors:0 dropped:0 overruns:0 carrier:0
          collisions:0 txqueuelen:1000
          RX bytes:34146 (33.3 KiB)  TX bytes:7018 (6.8 KiB)
          Interrupt:103 Base address:0xc000

lo        Link encap:Local Loopback
          inet addr:127.0.0.1  Mask:255.0.0.0
          inet6 addr: ::1%1/128 Scope:Host
          UP LOOPBACK RUNNING  MTU:65536  Metric:1
          RX packets:2723 errors:0 dropped:0 overruns:0 frame:0
          TX packets:2723 errors:0 dropped:0 overruns:0 carrier:0
          collisions:0 txqueuelen:1000
          RX bytes:207026 (202.1 KiB)  TX bytes:207026 (202.1 KiB)

sh-4.3#
```

No higher resolution available.

STM32MP15_example_command_local_terminal.png (800 × 480 pixels, file size: 53 KB, MIME type: image/png)

A quality version of this page, approved on 17 June 2020, was based off this revision.





Source
STMicroelectronics



File history

Click on a date/time to view the file as it appeared at that time.

	Date/Time	Thumbnail	Dimensions	User	Comment
current	08:46, 12 February 2019		800 × 480 (53 KB)	Maintenance script (talk contribs)	
	14:06, 13 November 2017		1,280 × 720 (65 KB)	Frp8988 (talk contribs)	

- You cannot overwrite this file.



File usage

The following 3 pages link to this file:

- [STM32MP15 Discovery kits - Starter Package](#)
- [STM32MP15 Evaluation boards - Starter Package](#)
- [Subpart - STM32MP15 - Starter Package](#)



Metadata

This file contains additional information, probably added from the digital camera or scanner used to create or digitize it. If the file has been modified from its original state, some details may not fully reflect the modified file.

Horizontal resolution	47.24 dpc
Vertical resolution	47.24 dpc