



SAI Linux driver



Contents

1. SAI Linux driver	
2. SAI internal peripheral	
3. ALSA overview	
4. Menuconfig or how to configure kernel	
5. SAI device tree configuration	
6. Debugfs	
7. Clock overview	
8. Pinctrl overview	



SAI Linux driver

Stable: 22.10.2019 - 08:02 / Revision: 22.10.2019 - 08:01

Contents

1 Article purpose	3
2 Short Description	3
3 Configuration	3
3.1 Kernel Configuration	3
3.2 Device tree	4
4 How to use	4
5 How to trace and debug	4
6 Source code location	4
7 References	5

1 Article purpose

This article introduces the SAI Linux[®] driver for the SAI internal peripheral.

2 Short Description

The SAI^[1] Linux driver is an ASoC CPU DAI driver implemented in the Linux ALSA framework.

3 Configuration

3.1 Kernel Configuration

Activate the SAI^[1] Linux driver in the kernel configuration using the Linux Menuconfig tool: Menuconfig or how to configure kernel.

```
[*] Device Drivers
  [*] Sound card support
    [*] Advanced Linux Sound Architecture
      [*] ALSA for SoC audio support
        STMicroelectronics STM32 SOC audio support
          [*] STM32 SAI interface (Serial Audio Interface) support
```



3.2 Device tree

Refer to the [SAI device tree configuration](#) article when configuring the SAI Linux kernel driver.

4 How to use

The SAI Linux driver can be accessed from userland through an ALSA device. Refer to [ALSA overview](#) for information on how to list and use ALSA devices.

5 How to trace and debug

The `debugfs` and `procfs` file system can be checked to get information on the SAI driver and the resources it uses. A non-exhaustive list of these file system entries is provided below. Refer to [ALSA overview](#) for more details on debugging tools.

- `debugfs` entries:
 - **asoc**: refer to [ALSA_overview#How_to_monitor](#)
 - **clk**: refer to [Clock_overview#How_to_monitor_with_debugfs](#) to get information on clocks.
 - **pinctrl**: refer to [Pinctrl_overview#How_to_monitor](#) to get information on pins.
 - **regmap**: allow to monitor SAI peripheral registers.

```
$ cat /sys/kernel/debug/regmap/xxx.audio-controller/registers
```

- `procfs` entries:
 - **asound**: refer to [ALSA_overview#How_to_debug](#)
 - **interrupts**: allow to check interrupts.

```
$ cat /proc/interrupts
```

6 Source code location

The STM32 SAI peripheral includes two independent audio subblocks that share common resources. The driver source code reflects this architecture.

`sound/soc/stm/stm32_sai.c` : handles common resources such as clock, interrupt, reset and shared register.

`sound/soc/stm/stm32_sai_sub.c` : handles the resources dedicated to each subblock.



7 References

- 1.01.1 SAI internal peripheral

Serial Audio Interface (Mechanism used to transfer non-buffered audio data between processors and/or audio converters.)

ALSA System on Chip

Central processing unit

Digital Audio Interface

Advanced Linux sound architecture

Process File System (See <https://en.wikipedia.org/wiki/Procsfs> for more details)

Debug File System (See <https://en.wikipedia.org/wiki/Debugfs> for more details)

Permission error

Stable: 21.01.2020 - 13:23 / Revision: 21.01.2020 - 13:21

You do not have permission to read this page, for the following reason:

The action "Read pages" for the draft version of this page is only available for the groups ST_editors, ST_readers, Selected_editors, sysop, reviewer

Permission error

Stable: 04.02.2020 - 07:47 / Revision: 04.02.2020 - 07:36

You do not have permission to read this page, for the following reason:

The action "Read pages" for the draft version of this page is only available for the groups ST_editors, ST_readers, Selected_editors, sysop, reviewer

Permission error

Stable: 31.01.2020 - 12:57 / Revision: 31.01.2020 - 12:52

You do not have permission to read this page, for the following reason:

The action "Read pages" for the draft version of this page is only available for the groups ST_editors, ST_readers, Selected_editors, sysop, reviewer

Permission error

Stable: 07.02.2020 - 10:43 / Revision: 07.02.2020 - 08:48



You do not have permission to read this page, for the following reason:

The action "Read pages" for the draft version of this page is only available for the groups ST_editors, ST_readers, Selected_editors, sysop, reviewer

Permission error

Stable: 04.02.2020 - 07:47 / Revision: 04.02.2020 - 07:34

You do not have permission to read this page, for the following reason:

The action "Read pages" for the draft version of this page is only available for the groups ST_editors, ST_readers, Selected_editors, sysop, reviewer

Permission error

Stable: 15.10.2019 - 11:58 / Revision: 15.10.2019 - 11:57

You do not have permission to read this page, for the following reason:

The action "Read pages" for the draft version of this page is only available for the groups ST_editors, ST_readers, Selected_editors, sysop, reviewer

Permission error

Stable: 30.01.2020 - 13:45 / Revision: 30.01.2020 - 13:43

You do not have permission to read this page, for the following reason:

The action "Read pages" for the draft version of this page is only available for the groups ST_editors, ST_readers, Selected_editors, sysop, reviewer