

Contents

1. Template:HighlightParam	2
2. Main Page	3

Template:HighlightParam

The content format pdf is not supported by the content model wikitext.

Return to [Main Page](#).

Page not found

SORRY, PAGE NOT FOUND

The page or document you requested is not available.

The URL entered might be no longer valid or the requested service may be temporarily unavailable.

To find the requested information:

- Verify the address has been entered correctly.
- Use the search function located in the page header.
- Make sure that you are properly logged in to see all wiki content.

[Back to Wiki homepage](#)

IMPORTANT NOTICE – READ CAREFULLY

STMicroelectronics NV and its subsidiaries ("ST") reserve the right to make changes, corrections, enhancements, modifications, and improvements to ST products and/or to this document at any time without notice. Purchasers should obtain the latest relevant information on ST products before placing orders. ST products are sold pursuant to ST's terms and conditions of sale in place at the time of order acknowledgment.

Purchasers are solely responsible for the choice, selection, and use of ST products and ST assumes no liability for application assistance or the design of purchasers' products.

No license, express or implied, to any intellectual property right is granted by ST herein.

Resale of ST products with provisions different from the information set forth herein shall void any warranty granted by ST for such product.

ST and the ST logo are trademarks of ST. For additional information about ST trademarks, refer to www.st.com/trademarks. All other product or service names are the property of their respective owners.

Information in this document supersedes and replaces information previously supplied in any prior versions of this document.

© 2023 STMicroelectronics – All rights reserved