

How to set up a Bluetooth connection

Stable: 11.02.2019 - 13:21 / Revision: 15.01.2019 - 11:12

1 How to setup Bluetooth

1.1 Setup

- Check that the driver has been probed correctly in the kernel log message

```
Board $>[ 0.923697] STM32 USART driver initialized
Board $>[ 0.928711] 4000e000.serial: ttyS1 at MMIO 0x4000e000 (irq = 42, base_baud = 60
```

- Check the Bluetooth interface

```
Board $> hciconfig -a
hci0: Type: Primary Bus: UART
      BD Address: 43:43:A1:12:1F:AC ACL MTU: 1021:8 SCO MTU: 64:1
      DOWN
      RX bytes:619 acl:0 sco:0 events:31 errors:0
      TX bytes:410 acl:0 sco:0 commands:31 errors:0
      Features: 0xbf 0xfe 0xcf 0xfe 0xdb 0xff 0x7b 0x87
      Packet type: DM1 DM3 DM5 DH1 DH3 DH5 HV1 HV2 HV3
      Link policy: RSWITCH SNIFF
      Link mode: SLAVE ACCEPT
```

1.2 Initialize the Bluetooth interface

```
Board $> hciconfig hci0 up
Board $> hciconfig -a
hci0: Type: Primary Bus: UART
      BD Address: AA:AA:AA:AA:AA:AA ACL MTU: 1021:8 SCO MTU: 64:1
      UP RUNNING
      RX bytes:1378 acl:0 sco:0 events:74 errors:0
      TX bytes:1186 acl:0 sco:0 commands:74 errors:0
      Features: 0xbf 0xfe 0xcf 0xfe 0xdb 0xff 0x7b 0x87
      Packet type: DM1 DM3 DM5 DH1 DH3 DH5 HV1 HV2 HV3
      Link policy: RSWITCH SNIFF
      Link mode: SLAVE ACCEPT
      Name: 'BlueZ 5.46'
      Class: 0x000000
      Service Classes: Unspecified
      Device Class: Miscellaneous,
      HCI Version: 4.1 (0x7) Revision: 0x0
      LMP Version: 4.1 (0x7) Subversion: 0x2209
      Manufacturer: Broadcom Corporation (15)
```

Universal Synchronous/Asynchronous Receiver/Transmitter

Universal Asynchronous Receiver/Transmitter

Automatic current limit (LCD power improvement solution)

Receive

Transmit

uniprocessor