

# How to setup wifi connection

Stable: 22.07.2019 - 08:57 / Revision: 19.07.2019 - 13:48

## Contents

1 ifconfig .....	1
1.1 Check WLAN interface .....	1
1.2 Initialize WLAN interface .....	2
2 iw .....	2
2.1 Scan available SSID (AP) .....	2
3 Wlan Network attachment (without system which manage systemd-networkd configuration) .....	3
3.1 Configure your WiFi connection .....	3
3.1.1 Connect to SSID .....	4
3.1.2 link to SSID .....	4
3.1.3 Assign IP address to WLAN interface .....	4
3.1.4 Check connectivity .....	4
4 Automatic WiFi configuration at start up .....	5
4.1 networkctl .....	5
4.2 How to set a wireless configuration with networkd .....	5

Even if the example is related to the RTL8723BU chip (this chip calls for a WiFi (minimally 802.11g/n) and Bluetooth 4.0 LE), most of the commands are generic ones and can be applied to any platform.

## 1 ifconfig

Verify the wlan0 interface is present (that means drivers have been started and the WiFi firmware loaded):

### 1.1 Check WLAN interface

```
Board $> ifconfig -a
lo          Link encap:Local Loopback
           LOOPBACK MTU:65536 Metric:1
           RX packets:0 errors:0 dropped:0 overruns:0 frame:0
           TX packets:0 errors:0 dropped:0 overruns:0 carrier:0
           collisions:0 txqueuelen:1000
           RX bytes:0 (0.0 B)  TX bytes:0 (0.0 B)
```

```
wlan0      Link encap:Ethernet  HWaddr 60:F1:89:3F:F6:0E
           BROADCAST MULTICAST MTU:1500 Metric:1
           RX packets:0 errors:0 dropped:0 overruns:0 frame:0
           TX packets:1 errors:0 dropped:0 overruns:0 carrier:0
           collisions:0 txqueuelen:1000
           RX bytes:0 (0.0 B)  TX bytes:10 (10.0 B)
```

## 1.2 Initialize WLAN interface

```
Board $> ifconfig wlan0 up
wlan0   Link encap:Ethernet  HWaddr 60:F1:89:3F:F6:0E
        inet addr:192.168.43.135  Bcast:192.168.43.255  Mask:255.255.255.0
        UP BROADCAST RUNNING MULTICAST  MTU:1500  Metric:1
        RX packets:19 errors:0 dropped:0 overruns:0 frame:0
        TX packets:19 errors:0 dropped:0 overruns:0 carrier:0
        collisions:0 txqueuelen:1000
        RX bytes:1774 (1.7 KiB)  TX bytes:2326 (2.2 KiB)
/* UP indica
```

## 2 iw

The next phase is to scan for any wireless access points with the command:

### 2.1 Scan available SSID (AP)

- Get only SSID name

```
Board $> iw dev wlan0 scan |grep SSID
        SSID: NETWORK1
        SSID: NETWORK2
```

- List full SSID information

```
Board $> iw dev wlan0 scan
BSS 00:23:5e:4a:28:f9(on wlan0)
    TSF: 0 usec (0d, 00:00:00)
    freq: 2412
    beacon interval: 100 TUs
    capability: ESS ShortPreamble ShortSlotTime (0x0421)
    signal: -72.00 dBm
    last seen: 0 ms ago
    SSID: NETWORK1
    Supported rates: 1.0* 2.0* 5.5* 6.0 9.0 11.0* 12.0 18.0
    DS Parameter set: channel 1
    TIM: DTIM Count 0 DTIM Period 1 Bitmap Control 0x0 Bitmap[0] 0x2
    Country: FR      Environment: Indoor/Outdoor
           Channels [1 - 13] @ 20 dBm
    BSS Load:
        * station count: 1
        * channel utilisation: 30/255
        * available admission capacity: 23437 [*32us]
    ERP: <no flags>
    Extended supported rates: 24.0 36.0 48.0 54.0
    WMM:
        * Parameter version 1
        * u-APSD
        * BE: CW 15-1023, AIFSN 3
        * BK: CW 15-1023, AIFSN 7
        * VI: CW 7-15, AIFSN 2, TXOP 3008 usec
        * VO: CW 3-7, AIFSN 2, TXOP 1504 usec
BSS 00:23:5e:96:57:20(on wlan0)
    TSF: 0 usec (0d, 00:00:00)
    freq: 2412
    beacon interval: 100 TUs
    capability: ESS Privacy ShortPreamble ShortSlotTime (0x0431)
    signal: -66.00 dBm
```

```
last seen: 0 ms ago
SSID: NETWORK2
Supported rates: 1.0* 2.0* 5.5* 6.0 9.0 11.0* 12.0 18.0
DS Parameter set: channel 1
Country: FR      Environment: Indoor/Outdoor
                Channels [1 - 13] @ 20 dBm
BSS Load:
    * station count: 8
    * channel utilisation: 48/255
    * available admission capacity: 23437 [*32us]
ERP: <no flags>
RSN:
    * Version: 1
    * Group cipher: CCMP
    * Pairwise ciphers: CCMP
    * Authentication suites: IEEE 802.1X 00-40-96:0
    * Capabilities: 4-PTKSA-RC 4-GTKSA-RC (0x0028)
Extended supported rates: 24.0 36.0 48.0 54.0
WMM:
    * Parameter version 1
    * u-APSD
    * BE: CW 15-1023, AIFSN 3
    * BK: CW 15-1023, AIFSN 7
    * VI: CW 7-15, AIFSN 2, TXOP 3008 usec
    * VO: CW 3-7, AIFSN 2, TXOP 1504 usec
```

## 3 Wlan Network attachment (without system which manage systemd-networkd configuration)

### 3.1 Configure your WiFi connection

Configure WiFi connection by using **wpa\_supplicant** tool

- Check current configuration

```
Board $> cat /etc/wpa_supplicant.conf
ctrl_interface=/var/run/wpa_supplicant
ctrl_interface_group=0
update_config=1
network={
    key_mgmt=NONE
}
```

- Set the WiFi network name and password

```
Board $> wpa_passphrase <your_ssid_name> <your_ssid_key> >> /etc/wpa_supplicant.conf
```

- Check new configuration

```
Board $> cat /etc/wpa_supplicant.conf
ctrl_interface=/var/run/wpa_supplicant
ctrl_interface_group=0
update_config=1
network={
    ssid="your_ssid_name"
    psk="your_ssid_key"
}
```



If no WPA key replace **psk=...** with **key\_mgmt=NONE**

### 3.1.1 Connect to SSID

```
Board $> wpa_supplicant -B -iwlan0 -c /etc/wpa_supplicant.conf  
Successfully initialized wpa_supplicant
```

### 3.1.2 link to SSID

```
Board $> iw wlan0 link  
SSID: NETWORK1  
freq: 2462  
RX: 501 bytes (3 packets)  
TX: 4056 bytes (22 packets)  
signal: -75 dBm  
tx bitrate: 12.0 MBit/s  
bss flags: short-preamble short-slot-time  
dtim period: 1  
beacon int: 100
```

### 3.1.3 Assign IP address to WLAN interface

Use the DHCP client to obtain an address (assuming wireless network (associated to) has a DHCP server):

```
Board $> dhclient wlan0
```

Use the ip command to verify the IP address assigned by the DHCP. The IP address is 192.168.43.135 from below.

```
Board $> ip addr show wlan0  
3: wlan0: mtu 1500 qdisc mq state UP qlen 1000  
link/ether 74:e5:43:a1:ce:65 brd ff:ff:ff:ff:ff:ff  
inet 192.168.43.135/24 brd192.168.1.255 scope global wlan0  
inet6 fe80::76e5:43ff:fea1:ce65/64 scope link  
valid_lft forever preferred_lft forever
```

### 3.1.4 Check connectivity

The most basic connectivity test is to use the “ping” command. In this example, the wireless router (associated to) has an IP address of 192.168.43.1:

```
Board $> ping 192.168.43.1
PING 192.168.43.1 (192.168.43.1): 56 data bytes
64 bytes from 192.168.43.1: seq=0 ttl=64 time=14.905 ms
64 bytes from 192.168.43.1: seq=1 ttl=64 time=30.387 ms
64 bytes from 192.168.43.1: seq=2 ttl=64 time=20.462 ms
```

- Note : Enter <CTRL+C> to terminate the ping session.

## 4 Automatic WiFi configuration at start up

### 4.1 networkctl

Systemd has a specific service for the network named **systemd-networkd**, this service comes with the tool **networkctl** which allows to show the status of each network interface.

```
Board $> networkctl --no-pager
IDX LINK          TYPE          OPERATIONAL SETUP
 1 lo              loopback      carrier    unmanaged
 2 eth0            ether         routable   configured
 3 sit0            sit           off        unmanaged
 4 ip6tnl0         tunnel6       off        unmanaged
 5 wlan0           wlan          off        unmanaged
 6 wlan1           wlan          off        unmanaged
```

6 links listed.

We can see that the **eth0** interface is managed by networked via the information **configured** and the interface is used (**routable**).

### 4.2 How to set a wireless configuration with networkd

The goal is to configure an wlan network interface via systemd-networkd configuration.

All the network configurations are stored on **/lib/systemd/network** or **/etc/systemd/network** Create the file dedicated to wireless interface:

```
Board $> cat /lib/systemd/network/51-wireless.network
[Match]
Name=wlan0

[Network]
DHCP=ipv4
```

For attaching this wireless interface to a specific network, we need to have some information like SSID of network and password.

To see the list of wireless network available:

```
Board $> ifconfig wlan0 up
Board $> iw dev wlan0 scan |grep SSID
        SSID: NETWORK1
        SSID: NETWORK2
```

Associate the wireless network to wireless interface, here wlan0:

```
Board $> mkdir -p /etc/wpa_supplicant/  
echo "ctrl_interface=/var/run/wpa_supplicant" > /etc/wpa_supplicant/wpa_supplicant-  
echo "eapol_version=1" >> /etc/wpa_supplicant/wpa_supplicant-wlan0.conf  
echo "ap_scan=1" >> /etc/wpa_supplicant/wpa_supplicant-wlan0.conf  
echo "fast_reauth=1" >> /etc/wpa_supplicant/wpa_supplicant-wlan0.conf  
echo "" >> /etc/wpa_supplicant/wpa_supplicant-wlan0.conf  
wpa_passphrase SSID_OF_NETWORK PASSWORD_OF_NETWORK >> /etc/wpa_supplicant/wpa_sup
```

Where **SSID\_OF\_NETWORK** **PASSWORD\_OF\_NETWORK** correspond to the SSID and password of wireless network.



the name of file on /etc/wpa\_supplicant must contains the name of wireless interface: wpa\_supplicant-**wlan0**.conf

To enable and start the wireless configuration:

```
Board $> systemctl enable wpa_supplicant@wlan0.service  
systemctl restart systemd-networkd.service  
systemctl restart wpa_supplicant@wlan0.service
```

Receive

Transmit

uniprocessor