



STM32MP1 Distribution Package - OpenSTLinux distribution



Contents

1. STM32MP1 Distribution Package - OpenSTLinux distribution	3
2. Category:Distribution Package	7
3. PC prerequisites	8
4. How to avoid proxy issues	8
5. Example of directory structure for Packages	8
6. STM32MP15 ecosystem release note - v1.1.0	8
7. STM32MP15 ecosystem release note	8
8. OpenEmbedded	8
9. STM32MP15 ecosystem release note - v1.0.0	9
10. U-Boot overview	9
11. ST-LINK	9



STM32MP1 Distribution Package - OpenSTLinux distribution

Stable: 21.02.2020 - 09:47 / Revision: 20.02.2020 - 09:44

This article aims to give the following information:

- How to download and install the **latest** OpenSTLinux distribution for the STM32 microprocessors Series
- Where to find the associated release note
- Where to find the previous releases (archives)



For more specific information, go through the [Distribution Package](#) article relative to your **STM32 microprocessors Series**: [Category:Distribution Package](#)

1 STM32MP15-Ecosystem-v1.1.0 release


- The STM32MP1 OpenSTLinux distribution is delivered through a manifest repository location and a manifest revision (**openstlinux-4.19-thud-mp1-19-10-09**).
- The installation relies on the `repo` command. In case the Repo tool (a Google-built repository management tool that runs on top of Git) is not yet installed and configured on the host PC, refer to the [PC prerequisites](#) article.
- The OpenSTLinux distribution is massively using open source software (OSS) packages that are downloaded from a variety of open source repositories; so it is required that the IT infrastructure proxies do not forbid such accesses. If some proxy-related issues are suspected, refer to the [How to avoid proxy issues](#) article.
- Install the STM32MP1 OpenSTLinux distribution


	STM32MP1 Distribution Package OpenSTLinux distribution - STM32MP15-Ecosystem-v1.1.0 release
	<ul style="list-style-type: none">• Go to the host PC directory where to install the Distribution Package (<i><Distribution Package installation directory></i>). Example, if following the proposition to organize the working directory: <pre>\$ cd <working directory path>/Distribution-Package</pre>• Create the OpenSTLinux distribution installation sub-directory: <pre>\$ mkdir openstlinux-4.19-thud-mp1-19-10-09 \$ cd openstlinux-4.19-thud-mp1-19-10-09</pre>• Initialize repo in the current directory (More details on 'repo init' here).
Installation	<pre>\$ repo init -u https://github.com/STMicroelectronics/oe-manifest.git -b refs/tags/openstlinux-4.19-thud-mp1-19-10-09</pre>



STM32MP1 Distribution Package OpenSTLinux distribution - STM32MP15-Ecosystem-v1.1.0 release	
	<p>Note: "ERROR 404" may appear during "repo init" command without any impact on the process</p> <ul style="list-style-type: none"> Synchronize the local project directories with the remote repositories specified in the manifest (more details on 'repo sync' here) <div style="border: 1px dashed black; padding: 10px; margin: 10px 0;"> <pre>\$ repo sync</pre> </div> <p>Note: <i>Distribution package</i> needs around 140MB to be installed (and around 25GB once <i>distribution package</i> is compiled).</p>
Release note	<p>Details about the content of this software package are available in the associated STM32MP15 ecosystem release note.</p> <p>If interested in previous releases, go through the archives of the ecosystem release note.</p>

- The **OpenSTLinux distribution installation directory** is in the *<Distribution Package installation directory>*, and is named `openstlinux-4.19-thud-mp1-19-10-09`:





Timesys layer for OpenEmbedded (standard)
Core metadata for current versions of OpenEmb

2 Archives

2.1 STM32MP15-Ecosystem-v1.0.0 release


- The STM32MP1 OpenSTLinux distribution is delivered through a manifest repository location and a manifest revision ([openstlinux-4.19-thud-mp1-19-02-20](#)).
- The installation relies on the `repo` command. In case the Repo tool (a Google-built repository management tool that runs on top of Git) is not yet installed and configured on the host PC, refer to the [PC prerequisites](#) article.
- The OpenSTLinux distribution is massively using open source software (OSS) packages that are downloaded from a variety of open source repositories; so it is required that the IT infrastructure proxies do not forbid such accesses. If some proxy-related issues are suspected, refer to the [How to avoid proxy issues](#) article.
- Install the STM32MP1 OpenSTLinux distribution


STM32MP1 Distribution Package OpenSTLinux distribution - STM32MP15-Ecosystem-v1.0.0 release	
Installation	<ul style="list-style-type: none">• Go to the host PC directory where to install the Distribution Package (<i><Distribution Package installation directory></i>). Example, if following the proposition to organize the working directory:
	<pre>\$ cd <working directory path>/Distribution-Package</pre>
	<ul style="list-style-type: none">• Create the OpenSTLinux distribution installation sub-directory:
	<pre>\$ mkdir openstlinux-4.19-thud-mp1-19-02-20 \$ cd openstlinux-4.19-thud-mp1-19-02-20</pre>
	<ul style="list-style-type: none">• Initialize repo in the current directory.
	Details: The below command downloads (in the <code>.repo</code> directory) the latest repo source code and a manifest file (<i>default.xml</i>) that describes the directory structure of the repositories for OpenSTLinux. The <code>-u</code> option specifies the manifest repository location, while the <code>-b</code> option specifies its branch.
	<pre>\$ repo init -u https://github.com/STMicroelectronics/oe-manifest.git -b refs/tags/openstlinux-4.19-thud-mp1-19-02-20</pre>



STM32MP1 Distribution Package OpenSTLinux distribution - STM32MP15-Ecosystem-v1.0.0 release	
	<p>Note: "ERROR 404" may appear during "repo init" command without any impact on the process</p> <ul style="list-style-type: none">• Synchronize the local project directories with the remote repositories specified in the manifest <p>Details:</p> <p>If a local project does not yet exist, the command clones a new local directory from the remote repository and sets up tracking branches as specified in the manifest.</p> <p>If the local project already exists, the command updates the remote branches and rebases any new local changes on top of the new remote changes.</p> <pre>\$ repo sync</pre>
Release note	<p>Details about the content of this software package are available in the associated STM32MP15 ecosystem release note.</p> <p>If interested in previous releases, go through the archives of the ecosystem release note.</p>

- The **OpenSTLinux distribution installation directory** is in the *<Distribution Package installation directory>*, and is named `openstlinux-4.19-thud-mp1-19-02-20`:





Open Source Software

Board support package

Microprocessor Unit

Advanced Linux sound architecture

Graphics Processing Units

Trusted Firmware for Arm Cortex-A

Das U-Boot -- the Universal Boot Loader (see [U-Boot_overview](#))

Open Graphics Library (See <http://www.opengl.org/> for more details)

Open Vector Graphics (See <http://www.khronos.org/openvg/> for more details)

Khronos Native Platform Graphics Interface (See <http://www.khronos.org/egl/> for more details)

ST in-circuit debugger and programmer for the STM8 and STM32 microcontroller families (See [ST-LINK](#) for more details)

Category:Distribution Package

This category groups together all articles related to a Distribution Package (whatever the microprocessor device and the board).

The Distribution Package is specified in the [Which Package better suits your needs](#) article.

Pages in category "Distribution Package"

The following 6 pages are in this category, out of 6 total.

H

- [How to add a customer application](#)
- [How to create your own machine](#)
- [How to cross-compile with the Distribution Package](#)
- [How to customize the Linux kernel](#)



S

- [STM32MP1 Distribution Package](#)
- [STM32MP1 Distribution Package for Android](#)

Permission error

Stable: 21.02.2020 - 08:23 / Revision: 14.02.2020 - 16:43

You do not have permission to read this page, for the following reason:

The action "Read pages" for the draft version of this page is only available for the groups ST_editors, ST_readers, Selected_editors, sysop, reviewer

Permission error

Stable: 26.09.2019 - 13:27 / Revision: 26.09.2019 - 13:26

You do not have permission to read this page, for the following reason:

The action "Read pages" for the draft version of this page is only available for the groups ST_editors, ST_readers, Selected_editors, sysop, reviewer

Permission error

Stable: 21.02.2020 - 08:27 / Revision: 19.02.2020 - 16:49

You do not have permission to read this page, for the following reason:

The action "Read pages" for the draft version of this page is only available for the groups ST_editors, ST_readers, Selected_editors, sysop, reviewer

Permission error

Stable: 02.04.2020 - 09:29 / Revision: 02.04.2020 - 09:24

You do not have permission to read this page, for the following reason:

The action "Read pages" for the draft version of this page is only available for the groups ST_editors, ST_readers, Selected_editors, sysop, reviewer

Permission error

Stable: 21.02.2020 - 13:34 / Revision: 21.02.2020 - 13:03

You do not have permission to read this page, for the following reason:

The action "Read pages" for the draft version of this page is only available for the groups ST_editors, ST_readers, Selected_editors, sysop, reviewer

Permission error



Stable: 29.01.2020 - 16:07 / Revision: 29.01.2020 - 16:06

You do not have permission to read this page, for the following reason:

The action "Read pages" for the draft version of this page is only available for the groups ST_editors, ST_readers, Selected_editors, sysop, reviewer

Permission error

Stable: 02.04.2020 - 09:50 / Revision: 02.04.2020 - 09:49

You do not have permission to read this page, for the following reason:

The action "Read pages" for the draft version of this page is only available for the groups ST_editors, ST_readers, Selected_editors, sysop, reviewer

Permission error

Stable: 23.01.2020 - 13:52 / Revision: 23.01.2020 - 13:46

You do not have permission to read this page, for the following reason:

The action "Read pages" for the draft version of this page is only available for the groups ST_editors, ST_readers, Selected_editors, sysop, reviewer

Permission error

Stable: 20.12.2019 - 15:12 / Revision: 12.12.2019 - 12:53

You do not have permission to read this page, for the following reason:

The action "Read pages" for the draft version of this page is only available for the groups ST_editors, ST_readers, Selected_editors, sysop, reviewer