



STM32MP15 microprocessor



Contents

1. STM32MP15 microprocessor	3
2. CRYIP internal peripheral	7
3. STM32MP15 resources	7
4. STM32MP15 peripherals overview	7
5. STM32MP15 boards	7
6. STM32MPU Embedded Software distribution	7
7. Category:STM32MPU Embedded Software distribution for Android	7



STM32MP15 microprocessor

Stable: 21.02.2020 - 08:35 / Revision: 12.02.2020 - 11:01

In a first part, this article shows the STM32MP157 line **part number codification** and **block diagram**. STM32MP157 belongs to STM32MP1 Series (refer to the list of part numbers provided below).

The second part of this article digs into technical aspects, and provides entry points to:

- STM32MP15 **documentation**
- articles dedicated to **Internal peripherals** that make the transition towards the software frameworks required to control these peripherals
- the list of **boards** supporting STM32MP15 devices
- the supported **software distributions**, that can be downloaded into the STM32MP15 device.

Contents

1 Introduction	3
2 Part number codification	3
2.1 STM32MP15x lines	4
2.2 Security and Cortex-A7 frequency	4
2.3 Packages	4
2.4 Junction temperature	4
3 Block diagram	5
4 Technical documentation	5
5 Internal peripherals	5
6 How to get further with STM32MP15 ecosystem	6
6.1 Boards	6
6.2 Supported software distributions	6
7 References and foot notes	6

1 Introduction

STM32MP15 microprocessors are based on the Arm® **Cortex®-A7** dual core. They support Trustzone mode for secure operations, a **Vivante GPU** and an Arm® **Cortex®-M4 coprocessor**.

Arm® Cortex®-M4 coprocessor and its peripheral set are directly inherited from the STM32 MCU family ^[1].

2 Part number codification

The table below shows the STM32MP15 microprocessor different part numbers available, together with their corresponding internal peripherals, security options and packages.



2.1 STM32MP15x lines

	Cortex-A7	Cortex-M4	GPU	Display	CAN
STM32MP151	Single	Yes	No	TFT	No
STM32MP153	Dual	Yes	No	TFT	Yes
STM32MP157	Dual	Yes	Yes	TFT/DSI	Yes

2.2 Security and Cortex-A7 frequency

	Security	Cortex-A7 frequency
STM32MP15xA	Basic	650 MHz ^[2]
STM32MP15xC	Secure boot + Cryptography (CRYP)	650 MHz ^[2]
STM32MP15xD	Basic	800 MHz ^{[2][3]}
STM32MP15xF	Secure boot + Cryptography (CRYP)	800 MHz ^{[2][3]}

2.3 Packages


STM32MP15xxAA	TFBGA448 18x18
STM32MP15xxAB	LFBGA354 16x16
STM32MP15xxAC	TFBGA361 12x12
STM32MP15xxAD	TFBGA257 10x10

2.4 Junction temperature

STM32MP15xxx1	- 20 to + 105 °C ^{[2][3]}
STM32MP15xxx3	- 40 to + 125 °C ^[2]

3 Block diagram

Here below is the STM32MP157F block diagram offering the richest features set of the STM32MP15 microprocessor.




4 Technical documentation

- [STM32MP15 Reference Manual: device and internal peripheral user specifications](#)
- [STM32MP15 Datasheet: electrical characteristics, package and pinout descriptions](#)

5 Internal peripherals

[STM32MP15 peripherals overview](#) article gives a description of all the internal peripherals available on STM32MP15 devices, with direct links to the articles where you can find:

- an overview of each peripheral
- the list of instances available for each peripheral type,
- information on the way each instance can be shared between Arm[®] Cortex[®]-A7 and Cortex[®]-M4 cores,
- direct links to the software frameworks used to control the peripheral from different Arm[®] cores and security modes such as Cortex[®]-A7 non secure, Cortex[®]-A7 secure or Cortex[®]-M4 (non secure).





6 How to get further with STM32MP15 ecosystem

6.1 Boards

The list of boards that integrate STM32MP15 devices can be found in [STM32MP15 boards](#) article.

6.2 Supported software distributions

 <p>STM32MPU Embedded Software distribution</p>	 <p>STM32MPU Embedded Software distribution for Android</p>
--	--

Click the links above to find information on:

- Distribution composition and associated software architecture
- Associated release notes

7 References and foot notes

- [STM32 MCU family](#)
- [2.02.12.22.32.42.5](#) Exposure to maximum rating conditions for extended periods may affect device reliability. Device mission profile (application conditions) is compliant with JEDEC JESD47 qualification standard. Refer to the [STM32MP15 Datasheet](#) and [AN5438](#) for further information.
- [3.03.13.2](#) 800 MHz part numbers are only available with '1' as junction temperatures range suffix (- 20 to + 105 °C).



Graphics Processing Units

Microcontroller Unit (MCUs have internal flash memory and are intended to operate with a minimum amount of external support ICs. They commonly are a self-contained, system-on-chip (SoC) designs.)

Controller Area Network (robust bus mainly used for automotive applications)

Display Serial Interface (MIPI® Alliance standard)

Permission error

Stable: 12.02.2020 - 16:40 / Revision: 12.02.2020 - 16:37

You do not have permission to read this page, for the following reason:

The action "Read pages" for the draft version of this page is only available for the groups ST_editors, ST_readers, Selected_editors, sysop, reviewer

Permission error

Stable: 21.02.2020 - 08:59 / Revision: 14.02.2020 - 10:13

You do not have permission to read this page, for the following reason:

The action "Read pages" for the draft version of this page is only available for the groups ST_editors, ST_readers, Selected_editors, sysop, reviewer

Permission error

Stable: 22.01.2020 - 16:15 / Revision: 22.01.2020 - 13:48

You do not have permission to read this page, for the following reason:

The action "Read pages" for the draft version of this page is only available for the groups ST_editors, ST_readers, Selected_editors, sysop, reviewer

Permission error

Stable: 22.01.2020 - 13:35 / Revision: 22.01.2020 - 13:32

You do not have permission to read this page, for the following reason:

The action "Read pages" for the draft version of this page is only available for the groups ST_editors, ST_readers, Selected_editors, sysop, reviewer

Permission error

Stable: 09.10.2019 - 09:37 / Revision: 26.09.2019 - 10:05

You do not have permission to read this page, for the following reason:

The action "Read pages" for the draft version of this page is only available for the groups ST_editors, ST_readers, Selected_editors, sysop, reviewer




Category:STM32MPU Embedded Software distribution for Android

STM32MPU Embedded Software distribution for Android™ is a set of software components (see [STM32MPU Embedded Software for Android architecture overview](#)), system build and development tools created to ease the development of applications on STM32 MPU devices (see [STM32 MPU devices](#)).

STM32MPU Embedded Software distribution for Android includes:

- a distribution for Android, running on Arm® Cortex®-A processors: [STM32MPU distribution for Android](#)
- an STM32Cube MPU Package, running on Arm® Cortex®-M processors: [STM32CubeMP1 Package](#)



STM32 supported device	Ecosystem release note	Boards	Starter Package	Developer Package	Distribution Package
STM32 MP15	STM32MP15 ecosystem release note	Evaluation boards	STM32MP15 Evaluation boards - Starter Package for Android	STM32MP1 Developer Package for Android	STM32MP1 Distribution Package for Android

If you are not yet familiar with **STM32MPU Embedded Software Packages**, please read [Which STM32MPU Embedded Software Package for Android better suits your needs](#).

Microprocessor Unit

Subcategories

This category has the following 2 subcategories, out of 2 total.



A

- Android distribution (2 P)

S

- STM32Cube MPU Package (3 P)