



STM32MP15 distribution for Android release note - v1.0.0



Contents

1. STM32MP15 distribution for Android release note - v1.0.0	3
2. STM32MPU distribution for Android	17
3. STM32MP15 ecosystem release note - v1.1.0	17
4. STM32MPU Embedded Software distribution for Android	17
5. STM32MP157C-EV1 - hardware description	17
6. STM32MP15 OpenSTLinux release note - v1.1.0	18
7. U-Boot overview	18



STM32MP15 distribution for Android release note - v1.0.0

Stable: 02.04.2020 - 08:52 / Revision: 02.04.2020 - 08:49

This article describes the content of STM32MPU distribution for Android **software** release version **st-android-9.0.0-2019-09-27** (tag), which is part of STM32MP15 ecosystem release note - v1.1.0.

Contents

1 Intended audience	4
2 Delivery scope and purpose	4
3 Licensing	4
4 Supported hardware	4
5 Delivered features	4
5.1 Main software components	4
5.2 Detailed features	5
5.2.1 BSP features	5
5.2.2 Android features	5
6 Recommendations for use	7
6.1 Safe use	7
6.2 Non-recommended use	7
7 Main restrictions list	7
7.1 BSP restrictions list	7
7.2 Android restrictions list	8
8 Minor release updates	8
9 How to get started with st-android-9.0.0-2019-09-27	8
10 Associated tools	8
11 Demo applications	9
11.1 STCopro M4Echo application	9
11.2 STCopro M4Example application	9
11.3 STCamera	9
11.4 STVideo	9
11.5 STPerf	9
12 Change log / Main changes	10
13 Detailed delivery content	10
13.1 Detailed description of STMicroelectronics modules	10
13.1.1 BSP modules	10
13.1.2 Common and peripherals modules	11
13.1.3 Board modules	15
13.1.4 Coprocessor service module	16
13.1.5 ST application modules	16



1 Intended audience

The targeted audience is STM32MP15 customers or partners.

2 Delivery scope and purpose

The STM32MPU distribution for Android™ provides all necessary components for running, developing and/or making your own platform based on Android™ framework. It runs on the Arm® Cortex®-A7 processors, and is a fundamental part of the STM32MPU Embedded Software distribution for Android.

It is compatible with **Android 9.0.0 (Pie)**.

It is provided as **example**. The Android certifications are not insured.

This delivery of STM32MP15 distribution for Android™ v1.0.0 is part of STM32MP15-Ecosystem-v1.1.0 (see the STM32MP15 ecosystem release note - v1.1.0).

3 Licensing

This software package is licensed under a SOFTWARE LICENSE AGREEMENT (SLA). Customers may not use this package except in compliance with the **software license agreement (SLA)**.

All of the packages use the same source components. All components and their respective licenses are listed **here**.

4 Supported hardware

This software delivery is compatible with the following boards:

- STM32MP157C-EV1 Evaluation board. For more information on this board, please read the article [STM32MP157C-EV1 - hardware description](#)

5 Delivered features

5.1 Main software components

- Android version v9.0.0 (AOSP android-9.0.0_r46 tag)



- Kernel version v4.19.49 (AOSP common kernel) + updates for STM32MP1 and associated boards (waiting upstream finalization)
- TF-A version v2.0 + updates for STM32MP1 and associated boards (waiting upstream finalization)
- U-Boot version v2018.11 + updates for STM32MP1 and associated boards (waiting upstream finalization)
- OP-TEE version v3.3.0 + updates for STM32MP1 and associated boards (waiting upstream finalization)
- STM32CubeMP1 FW v1.1.0
- GCC version v8.2
- openOCD version v0.10.0
- GCnano version v6.2.4

5.2 Detailed features

5.2.1 BSP features

The *STM32MP15 distribution for Android™* v1.0.0 is based on the OpenSTLinux BSP v1.1.0 described in the following chapters:

- [Linux Kernel](#)
- [U-Boot secondary bootloader](#)
- [TF-A primary bootloader](#)
- [OP-TEE trusted environment](#)

5.2.2 Android features

Domain	Feature	STM32MP15 Evaluation board	Comment
Boot	Fastboot	✓	Entering this mode through connect ST-Link console (uart) or by HW control
	Verified boot	✗	
	A/B mechanism	✗	A/B images available but boot on A by default
	Recovery	✗	
Multimedia	Audio speaker	✓	audio speaker output can be used only to connect headset
	Audio headset	✓	not selected by default (no headset detection)
	Audio built-in digital micro	✓	limited to one microphone (mono)
	Audio USB	✗	
	Camera	✓	
	Camera USB	✗	
	Video SW decode	✓	480p30 max. without audio
	SELinux	✓	



Domain	Feature	STM32MP15 Evaluation board	Comment
Security	Runtime verification	✘	
	Disk encryption	✘	
	Trusted environment	✔	OP-TEE
	Keystore	✘	only software backup used
	Gatekeeper	✘	
Network and connectivity	Ethernet	✔	
	Wifi	✔	Using TP-LINK dongle (TL-WN722N) for test purpose
	Wifi hotspot	✘	
	BT / BLE	✘	
	USB	✔	Mass storage / MTP / PTP
Systems	Boot control	<i>Partially</i>	Available but not enable
	Power control	✔	
	Thermal control	✔	Only one temperature managed for CPU/GPU (others are stubbed)
	Update engine	✘	
Sensors	Accelerometer	✘	
	Gyroscope	✘	
	Magnetometer	✘	
	Proximity	✘	
	Pressure	✘	
	Temperature	✘	
	Hub	✘	
Debug	ADB (USB)	✔	
	ADB (Ethernet)	✔	
	ADEB	✔	Only for SELinux trace
	Perfetto	✔	Several limitations with Android 9.0.0
	SYSTRACE	✔	
	Metrics	✘	



Domain	Feature	STM32MP15 Evaluation board	Comment
Storage	USB Key	✓	
	microSD card	✓	
	eMMC	✓	
Others	Lights	✓	
	Touchscreen	✓	

6 Recommendations for use

6.1 Safe use

- Flash-load and boot from all supported Flash devices: SDCard and eMMC Flash memories
- Develop Android™ applications, libraries, kernel modules...
- Prototype applications based on ST boards
- Develop your own board based on STM32MP15x

6.2 Non-recommended use

- None

7 Main restrictions list

7.1 BSP restrictions list

- CubeMX configuration panels propose some internal peripheral modes not supported by TF-A or OP-TEE drivers running in Cortex-A7 secure context.
- The following table lists all known restrictions.

IP	Information/Restriction usage in Cortex-A7 secure context
I2C4 /I2C6	The SMBus-two-wire-Interface mode proposed is not supported for Cortex-A7 secure context (TF-A , OP-TEE) as no use case foreseen
PWR	TF-A and OP-TEE implementation do not support wake-up events for secure IPs assigned to Cortex-A7 secure context
RCC	The master clock output1 et 2, Audio clock input modes proposed are not applicable for Cortex-A7 secure context (TF-A, OP-TEE)



IP	Information/Restriction usage in Cortex-A7 secure context
SPI6	The SPI SW driver is not available in OP-TEE implementation for Cortex-A7 secure context
TAMP	OP-TEE implementation does not support TAMP_IN inputs and TAMP_OUT outputs in Cortex-A7 secure context
USAR T1	OP-TEE implementation does not support USART synchronous mode in Cortex-A7 secure context

7.2 Android restrictions list

STM32P15 distribution for Android™ is provided as example.

In this context:

- Android 9.0.0 with Linux Kernel 4.19 is not an association officially supported by the frameworks (several limitations to be expected)
- Compliance tests (VTS/CTS) are not insured (but they are executed and treated as much as possible)
- Security HAL (Keystore, Gatekeeper, Oemlock) are not available (removed from manifest) or stubbed
- Verified Boot and A/B boot mechanism not available (or partially)

Available on STM32MP15 Evaluation Board but not integrated in STM32P15 distribution for Android™:

- Audio headset detection is not available (need to force the usage)
- Audio RCA is not available (SPDIF input / SPDIF output)
- Audio digital microphone is limited to mono (record usage)
- Joystick is not available

8 Minor release updates

STMicroelectronics can delivers corrections on purpose through github® components.

9 How to get started with st-android-9.0.0-2019-09-27

Refer to [How to get the software and start with this release.](#)

10 Associated tools

Refer to the [Referenced tools release notes](#) .



11 Demo applications

The STM32MP15 distribution for Android™ is delivered with several applications provided as example.

11.1 STCopro M4Echo application

Example of application using the proprietary coprocessor service (allow direct interaction with the firmware started on the embedded Arm® Cortex®M4).

The firmware just returns the received character on the opened serial port.

The associated application project is available on github® (compatible with Android Studio IDE): [STCoproM4Echo application](#).

11.2 STCopro M4Example application

Example of application using the proprietary coprocessor service (allow direct interaction with the firmware started on the embedded Arm® Cortex®M4).

The firmware generates a signal on the DAC and get back a signal from the ADC. A wire can be added to loop the DAC on ADC. The firmware shows also a simple usage of several blocks available on Arm® Cortex®M4 side.

The associated application project is available on github® (compatible with Android Studio IDE): [STCoproM4Example application](#).

The associated firmware project is available on github® (compatible with System Workbench IDE): [STCoproM4Example firmware](#).

11.3 STCamera

Simple Camera application (preview) used to show a way to manage the built-in camera, only compatible with MB1379 camera extension board. An external storage configured as portable device shall be available to allow taking a picture.

11.4 STVideo

Simple Video application used to show a way to play a video. The video files shall be stored in the directory *Movies* of an external storage (ex: USB key) configured as portable device.

11.5 STPerf

Performance overlay application used to show in foreground the device performances (CPU usage, GPU usage, frame rate). The settings and stop commands are available on notifications system interface.



12 Change log / Main changes

Initial version.

13 Detailed delivery content

13.1 Detailed description of STMicroelectronics modules

13.1.1 BSP modules

Module name	Path of module	Description
stm32mp1-bootloader	device/stm32mp1-bootloader	Primary (Trusted Firmware-A) and secondary (Universal Boot Loader for embedded devices) bootloaders for STM32MP
		STM32MP U distribution for Android licenses - v1.0.0
		STM32MP U distribution for Android licenses -



Module name	Path of module	Description						
		v1.0.0						
stm32mp1-kernel	device/stm32mp1-kernel	Linux STM32MP Kernel STM32MP U distribution for Android licenses - v1.0.0						
stm32mp1-tee	device/stm32mp1-tee	OPTEE OS for STM32MP STM32MP U distribution for Android licenses - v1.0.0						
stm32mp1-openocd	device/stm32mp1-openocd	Free and Open On-Chip Debugging, In-System Programming and Boundary-Scan Testing						
<table border="1"> <thead> <tr> <th>Name</th> <th>Version</th> <th>License</th> </tr> </thead> <tbody> <tr> <td>stm32mp1-openocd</td> <td>0.10.0</td> <td>GPLv2</td> </tr> </tbody> </table>			Name	Version	License	stm32mp1-openocd	0.10.0	GPLv2
Name	Version	License						
stm32mp1-openocd	0.10.0	GPLv2						

13.1.2 Common and peripherals modules

Module name	Path of module	Description
stm32mp1	device	Configuratio



Module name			Path of module	Description
			ce /stm / stm3 2mp1	n of the STM32MP1 distribution for Android
Name	Version	License		
stm32mp1	NA	Apache v2.0		
allocator			devi ce / stm / stm 32mp 1/ peri pher al / all ocat or	STMicroele ctronics allocator H AL public header files useful for composer
Name	Version	License		
allocator	NA	Apache v2.0		
audio			devi ce / stm / stm 32mp 1/ peri pher al	STMicroele ctronics Audio HAL source code
Name	Version	License		
audio	NA	Apache v2.0		
bootctrl			devi ce / stm / stm 32mp 1/ peri pher al / boo tctr l	STMicroele ctronics Boot Control HA L source code and the dedicated misc partition image generator



Module name			Path of module	Description						
<table border="1"> <thead> <tr> <th>Name</th> <th>Version</th> <th>License</th> </tr> </thead> <tbody> <tr> <td>bootctrl</td> <td>NA</td> <td>Apache v2.0</td> </tr> </tbody> </table>			Name	Version	License	bootctrl	NA	Apache v2.0		
Name	Version	License								
bootctrl	NA	Apache v2.0								
camera			device/stm32mp1/peripheral	STMicroelectronics Camera HAL source code						
<table border="1"> <thead> <tr> <th>Name</th> <th>Version</th> <th>License</th> </tr> </thead> <tbody> <tr> <td>camera</td> <td>NA</td> <td>Apache v2.0</td> </tr> </tbody> </table>			Name	Version	License	camera	NA	Apache v2.0		
Name	Version	License								
camera	NA	Apache v2.0								
composer			device/stm32mp1/peripheral	STMicroelectronics composer HAL source code						
<table border="1"> <thead> <tr> <th>Name</th> <th>Version</th> <th>License</th> </tr> </thead> <tbody> <tr> <td>composer</td> <td>NA</td> <td>Apache v2.0</td> </tr> </tbody> </table>			Name	Version	License	composer	NA	Apache v2.0		
Name	Version	License								
composer	NA	Apache v2.0								
copro			device/stm32mp1/peripheral	STMicroelectronics Copro HAL source code						
<table border="1"> <thead> <tr> <th>Name</th> <th>Version</th> <th>License</th> </tr> </thead> <tbody> <tr> <td>copro</td> <td>NA</td> <td>Apache v2.0</td> </tr> </tbody> </table>			Name	Version	License	copro	NA	Apache v2.0		
Name	Version	License								
copro	NA	Apache v2.0								
health			device/stm32mp1/peripheral	STMicroelectronics Health hardware service source code						
<table border="1"> <thead> <tr> <th>Name</th> <th>Version</th> <th>License</th> </tr> </thead> <tbody> <tr> <td>health</td> <td>NA</td> <td>Apache v2.0</td> </tr> </tbody> </table>			Name	Version	License	health	NA	Apache v2.0	/health	
Name	Version	License								
health	NA	Apache v2.0								



Module name			Path of module	Description
lights			device/stm32mp1/peripheral	STMicroelectronics Lights HAL source code
Name	Version	License		
lights	NA	Apache v2.0		
memtrack			device_s/stm32mp1/peripheral	STMicroelectronics Memtrack HAL source code
Name	Version	License		
memtrack	NA	Apache v2.0		
oemlock			device_ac/stm32mp1/peripheral	STMicroelectronics OemLock HAL source code (stub version)
Name	Version	License		
oemlock	NA	Apache v2.0		
thermal			/oemdevice/stm32mp1/peripheral/thermal	STMicroelectronics Thermal hardware service source code
Name	Version	License		
thermal	NA	Apache v2.0		
usb			device	STMicroelectronics



Module name			Path of module	Description
			/stm32mp1/peripheral/usb	Usb hardware service source code
Name	Version	License		
usb	NA	Apache v2.0		
wifi			device/stm32mp1/peripheral/wifi	STMicroelectronics libwifi HAL source code
Name	Version	License		
wifi	NA	Apache v2.0		

13.1.3 Board modules

Module name			Path of module	Description
eval			device/stm32mp1/eval	STMicroelectronics configuration for Android used to generate images adapted to the STM32MP15 Evaluation boards
Name	Version	License		
eval	NA	Apache v2.0		

**13.1.4 Coprocessor service module**

Module name			Path of module	Description
CoproService			packages/ apps/ CoproService	STMicroelectronics coprocessor service
Name	Version	License		
CoproService	NA	Apache v2.0		

13.1.5 ST application modules

Module name			Path of module	Description
app			vendor/ stm/ app	STMicroelectronics applications associated if required to their respective coprocessor firmware
Name	Version	License		
app	NA	Apache v2.0		

Android Open Source Project

Trusted Firmware for Arm Cortex-A

Das U-Boot -- the Universal Boot Loader (see [U-Boot_overview](#))

Open Portable Trusted Execution Environment

Board support package

spelling for older versions of STLink

BlueTooth

Bluetooth Low Energy. Bluetooth LE, marketed as Bluetooth Smart is a wireless personal area network technology designed and marketed by the Bluetooth Special Interest Group aimed at novel applications in the healthcare, fitness, beacons, security, and home entertainment industries.

Central processing unit



STM32MP15 distribution for Android release note - v1.0.0

Graphics Processing Units

Android debug bridge (Android specific)

former spelling for eMMC ('e' in italic)

Flash memory shortened to gain space in titles, tables and block diagrams

System Management Bus

Reset and Clock Control

Serial Peripheral Interface

Tamper

Universal Synchronous/Asynchronous Receiver/Transmitter

Vendor Test Suite (Android specific)

Compatibility Test Suite (Android specific) or Clear to send (in UART context)

Hardware Abstraction Layer

(Software)Integrated development/design/debugging environment

Digital-to-analog converter (Electronic circuit that converts a binary number into a continuously varying value.)

Analog-to-digital converter. The process of converting a sampled analog signal to a digital code that represents the amplitude of the original signal sample.

Operating System

Non Applicable

STM32MPU distribution for Android

Stable: 09.10.2019 - 12:45 / Revision: 06.09.2019 - 07:20

Invalid target: no reviewed revision corresponds to the given ID.

[Return to STM32MPU distribution for Android.](#)

STM32MP15 ecosystem release note - v1.1.0

Stable: 02.04.2020 - 09:29 / Revision: 02.04.2020 - 09:24

Invalid target: no reviewed revision corresponds to the given ID.

[Return to STM32MP15 ecosystem release note - v1.1.0.](#)

STM32MPU Embedded Software distribution for Android

Stable: 09.10.2019 - 12:44 / Revision: 08.10.2019 - 08:12

Invalid target: no reviewed revision corresponds to the given ID.

[Return to STM32MPU Embedded Software distribution for Android.](#)



STM32MP157C-EV1 - hardware description

Stable: 25.10.2019 - 09:04 / Revision: 25.10.2019 - 09:04

Invalid target: no **reviewed** revision corresponds to the given ID.

Return to [STM32MP157C-EV1 - hardware description](#).

STM32MP15 OpenSTLinux release note - v1.1.0

Stable: 02.04.2020 - 10:09 / Revision: 02.04.2020 - 10:06

Invalid target: no **reviewed** revision corresponds to the given ID.

Return to [STM32MP15 OpenSTLinux release note - v1.1.0](#).

U-Boot overview

Stable: 23.01.2020 - 13:52 / Revision: 23.01.2020 - 13:46

Invalid target: no **reviewed** revision corresponds to the given ID.

Return to [U-Boot overview](#).